



info@milkbareurope.com **milkbareurope.com**

Milk Bar® 5

The Milk Bar 5 was the first group feeding gravity feeder! Ever. Anywhere. The Milk Bar 5 comes fully assembled with teats fitted and ready to use.

Milk Bar Code 910200

Volume: 15L

Weight: 2kg

Length: 300mm

Height: 360mm

Width: 300mm



Carry Handle

Sturdy carry handle for easy handling.

Self Latching Catch

The catch drops down to hold the feeder in place.

Moulded Hooks

The hooks are moulded to sit on 25m or 40mm rails.

Gradients

Three 5L steps are moulded into the feeder.



Milk Bar Plug 22

Milk Bar Code 900109

Use a Milk Bar Plug to seal off any spare teat holes.



Teats do not need to be removed or flushed through for cleaning.

Daily: Rinse feeders with cold water.

Twice a week: Scrub feeders with hot water (50°C) and Alkali Detergent.

Bend the teats with your brush to flush the milk out of the teat.

Rinse with clean water.

